

This Datasheet is for the

# IC693ALG220

Analog Voltage Input - 4 Channel

http://www.qualitrol.com/shop/p-14570-ic693alg220.aspx

# Provides the wiring diagrams and installation guidelines for this GE Series 90-30 module.

For further information, please contact Qualitrol Technical Support at

1-800-784-9385

support@qualitrol.com

Chapter 10

# Analog Input Modules

### Analog Voltage Input - 4 Channel IC693ALG220

The **4-Channel Analog Voltage Input** module for the Series 90-30 Programmable Logic Controller provides four input channels, each capable of converting an analog input signal to a digital signal for use as required by your application. The Analog Voltage Input module is capable of converting inputs in the range of -10 to +10 volts. Conversion speed for each of the four channels is one millisecond. This provides an update rate of four milliseconds for any channel. Resolution of the converted signal is 12 bits binary (1 part in 4096).

User data in the %AI registers is in 16-bit 2's complement format. The placement of the 12 bits from the A/D converter in the %AI data word is shown below. The relationship between the voltage input and the data from the A/D converter is shown in Figure 3-10.

| MSB |     |    |    | -  |    | _  |    | _  | -  |    | -  |   |   | _ | LSB |
|-----|-----|----|----|----|----|----|----|----|----|----|----|---|---|---|-----|
| S   | D10 | D9 | D8 | D7 | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Х | X | X | Х   |

X = not applicable to this discussion.

S = sign bit




Figure 10-1. A/D Bits vs. Voltage Input

Scaling of the input is shown below in Figure 3-11.




Figure 10-2. Scaling for Voltage Input

A limited current input mode is also provided in the module. A jumper is provided on the user terminal connector for each channel, which may be used to connect the internal 250 ohm shunt resistor into the circuit. The shunt resistor effectively provides a -40 to +40 mA current input range. However, the input current should generally not exceed  $\pm 20$  mA, to avoid self-heating of the input resistor and a corresponding loss of accuracy. A 4 to 20 mA input corresponds to a 1 to 5 volt input to the voltage input module; therefore, the resolution of the 4 to 20 mA input signal is approximately 10 bits binary (1 part in 1024). The resolution can be increased to approximately 11 bits (1 part in 2048) by using a precision 250 ohm resistor in place of the jumper. The resistor causes the voltage input module to see a 4 to 20 mA input as 2 to 10 volts.

The main power source for the module is derived from the isolated +24 VDC power supplied by the PLC power supply. This voltage is routed through an inverter/regulator to produce the operating voltages for the module. This module also consumes 27 mA from the +5 VDC output of the PLC power supply. An LED at the top of the module's faceplate is ON when the module's power supply is operating. The module provides electrical isolation of externally generated noise between the field wiring and the backplane through optical isolation.

To minimize the capacitive loading and noise, all field connections to the module should be wired using a good grade of twisted, shielded instrumentation cable. The shields can be connected to either COM or GND. The COM connection provides access to the common of the analog circuitry in the module. The GND connection provides access to the baseplate (frame ground).

This module can be installed in any I/O slot of a 5 or 10-slot baseplate in a Series 90-30 PLC system. See page 3-11 to determine the number of Analog Voltage Input modules that can be installed in a system.

#### Note

Connect the + and – terminals together for all unused inputs in order to minimize any fluctuations in the analog input table for the unused points.

10

| Voltage Range                  | $-10$ to $+10$ volts $\ddagger$   |
|--------------------------------|---|
| Calibration                    | Factory calibrated  |
| Update Rate                    | 4 msec (all four channels)  |
| Resolution                     | $5 \text{ mV}/20 \mu\text{A}$ , (1 LSB = $5 \text{ mV}$ )                 |
| Absolute Accuracy ‡            | $\pm 10 \text{ mV}/40 \mu\text{A}$ (typical) over operating temperature   |
|                                | $\pm 30 \text{ mV}/160  \mu\text{A}$ (maximum) over operating temperature |
| Linearity                      | < 1 Least Significant Bit   |
| Isolation                      | 1500 volts between field side and logic side                              |
| <b>Cross-Channel Rejection</b> | > 80 db   |
| Input Impedance                | > 9 Megohms (voltage mode)  |
|                                | 250 ohms (current mode)   |
| Input Filter Response          | 17 Hz   |
| Internal Power Consumption     | 27 mA from +5 volt bus on the backplane                                   |
|                                | 98 mA from the isolated +24 volt backplane bus                            |

Table 10-1. Specifications for Analog Voltage Input Module - IC693ALG220


Refer to Appendix C for product standards and general specifications.


 $\ddagger$  Both inputs must be within  $\pm$  11 volts of COM, including any noise present on the inputs.

 $\ddagger$  In the presence of severe RF interference (IEC 801-3, 10V/m), accuracy may be degraded to  $\pm$ 100 mV/400  $\mu$ A.

# **Analog Voltage Input Block Diagram**


The following figure is a block diagram of the 4-Channel Analog Voltage Input Module.





# IC693ALG220 Analog Input Module Field Wiring Information

The following figure provides information for connecting field wiring to the 4-Channel Analog Voltage Input module.



#### Figure 10-4. Field Wiring for 4-Channel Analog Voltage Input Module

#### Note

The (–) side of the voltage source can also be tied to the COM terminal if the source is floating to limit common-mode voltages. The COM connection provides access to the common of the analog circuitry in the module. The GND connection provides access to the baseplate (frame ground).

Please refer to Chapter 2 for wiring and shield ground connection details.

# Analog Current Input - 4 Channel IC693ALG221

The **4-Channel Analog Current Input module** for the Series 90-30 Programmable Logic Controller provides four input channels, each capable of converting an analog input signal to a digital signal for use as required by your application. This module provides two input ranges. The default range is 4 to 20 mA with user data scaled so that 4 mA corresponds to a count of 0 and 20 mA corresponds to a count of 32000 with each 1000 counts representing 0.5 mA. When a jumper is added to the I/O terminal board, the input range is changed to 0 to 20 mA with user data scaled so that 0 mA corresponds to a count of 32000 with each 320 mA corresponds to a count of 32000 with each 800 counts representing 0.5 mA. Two range jumpers are provided with the module; one for channels one and two, and the other for channels three and four.

Conversion speed for each of the four channels is one-half millisecond. This provides an update rate of two milliseconds for any channel. Resolution of the converted signal is 12 bits binary (1 part in 4096) over either range. User data in the %AI registers is in 16-bit 2's complement format. The placement of the 12 bits from the A/D converter in the %AI data word is shown below. The relationship between the current input and the data from the A/D converter is shown in Figures 3-14 and 3-15.

| MSB | _   |     |    |    |    |    |    |    |    |    |    |    |   |   | LSB |
|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|---|---|-----|
| Х   | D11 | D10 | D9 | D8 | D7 | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Х | Х | Х   |

X=not applicable to this discussion.




Figure 10-5. A/D Bits vs. Current Input

If the current source is reversed into the input, or is less than the low end of the current range, then the module will output a data word corresponding to the low end of the current range (0000H in %AI). If an input that is out of range is entered (that is, it is greater than 20 mA), the A/D converter will output up to full scale (corresponding to 7FF8H in %AI).

Input scaling is shown in the next figure.




Figure 10-6. Scaling for Analog Current Input

Input protection for the module is sufficient to guarantee operation with reduced performance with up to 200V common-mode. The module provides electrical isolation of externally generated noise between field wiring and the backplane through the use of optical isolation.

To minimize the capacitive loading and noise, all field connections to the module should be wired using a good grade of twisted, shielded instrumentation cable. The shields can be connected to either COM or GND. The COM connection provides access to the common of the analog circuitry in the module. The GND connection provides access to the baseplate (frame ground).

An LED at the top of the faceplate is ON when the module's power supply is operating. The main power source for the module is the isolated +24 VDC power supplied by the PLC power supply. This voltage is routed through an inverter/regulator to provide the operating voltage for the module. This module also consumes power from the +5 VDC output of the PLC power supply to drive the isolation circuitry. This module can be installed in any I/O slot of a 5 or 10-slot baseplate in a Series 90-30 PLC system. See page 3-11 to determine the number of Analog Current Input modules that can be installed in a system.


| Input Current Ranges              | 4 to 20 mA and 0 to 20 mA                      |  |  |  |  |  |
|-----------------------------------|--|--|--|--|--|--|
| Calibration                       | Factory calibrated to 4 µA per count           |  |  |  |  |  |
| Update Rate                       | 2 msec (all four channels)                     |  |  |  |  |  |
| Resolution at 4-20 mA             | $4 \mu\text{A} (1 \text{LSB} = 4 \mu\text{A})$ |  |  |  |  |  |
| Resolution at 0-20 mA             | $5 \mu A (1  \text{LSB} = 5 \mu A)$            |  |  |  |  |  |
| Absolute Accuracy †               | 0.1% full scale + $0.1%$ reading               |  |  |  |  |  |
| <b>Common Mode Voltage</b>        | 200 volts                                      |  |  |  |  |  |
| Linearity                         | < 1 Least Significant Bit                      |  |  |  |  |  |
| Isolation                         | 1500 volts between field side and logic side   |  |  |  |  |  |
| <b>Common Mode Rejection</b>      | > 70 db at DC; >70 db at 60 Hz                 |  |  |  |  |  |
| <b>Cross-Channel Rejection</b>    | > 80 db from DC to 1 kHz                       |  |  |  |  |  |
| Input Impedance                   | 250 ohms                                       |  |  |  |  |  |
| Input Filter Response             | 325 Hz   |  |  |  |  |  |
| <b>Internal Power Consumption</b> | 100 mA from the isolated +24 volt supply       |  |  |  |  |  |
|                                   | 25 mA from+5 volt bus on the backplane         |  |  |  |  |  |

Table 10-2. Specifications for Analog Current Input Module - IC693ALG221

Refer to Appendix B for product standards and general specifications.

 $\ddagger$  In the presence of severe RF interference (IEC 801-3, 10V/m), accuracy may be degraded to  $\pm 0.5\%$  FS.

# IC693ALG221 Analog Current Input Block Diagram




The following figure is a block diagram of the 4-Channel Analog Current Input Module.

Figure 10-7. Analog Current Input Module Block Diagram - IC693ALG221

# IC693ALG221 Analog Input Module Field Wiring Information

The following figure provides information for connecting field wiring to the user terminal board on the 4-Channel Analog Current Input Module.



#### Figure 10-8. Field Wiring for 4 Channel Analog Current Input Module

#### Note

In order to limit common-mode voltages, each current source common line may also be tied to its associated COM terminal if the source is floating. These optional connections are shown in the figure above.

Please refer to Chapter 2 for wiring and shield ground connection details.